BRANSON

Bransonic[®] CPX Ultrasonic Baths

General Description

Bransonic CPX ultrasonic baths feature digital controls with power tracking capabilities to adjust for light or heavy loads, high/low power control, degassing and sleep mode.

The CPX baths offer the following features:

- Sweep frequency eliminates standing waves and creates consistent cavitation throughout the tank.
- 40 kHz rugged industrial transducers.
- 99-minute digital timer with continuous ultrasonic operation.
- Ultrasonic power tracking: The new CPX Series Bransonic control circuitry actively tracks the operating frequency of the bath and immediately brings the tank's frequency back to its optimum point. What this means to the end user is that the CPX Series Bransonic bath will always deliver the *same ultrasonic power* without depending on the operator to make adjustments. The new CPX Series Bransonic delivers unwavering cavitation, steady activity in the bath, even when the load conditions change.
- **Degassing and conditioning the solution:** The CPX degassing period can be set up to 99 minutes. Extended degas time periods allow for "beyond cleaning" applications such as sample preparation, which includes degassing liquids, mixing and homogenization, dissolving solids, cell lysing, and dispersion of particles.

Consult with your Branson representative about the Bransonic accessories and solution best suited for your application needs. **Visit us at www.Bransonic.com**



- High/low power control: When cleaning delicate parts, the CPX unit allows the user to lower the amplitude of the acoustic energy in the bath: 100% power to the tank for normal applications, 70% power for delicate applications. Manipulating the output waveform in this manner greatly helps to avoid damage to the components in the bath during the ultrasonic process.
- **Sleep mode:** An energy-saving green feature. When the cycle is complete and no control keys are touched for 15 minutes, the CPX unit goes into sleep mode. Touching any key on the controller causes the unit to come back on.
- Controls are located above and behind the cleaning tank in an easily accessible control tower panel, and raised above the tank to avoid damage from cleaning solutions.
- Convenient built-in pour drains are featured on .5- and .75gallon models. Tank drains with valves are incorporated on models 1.5-gallon and larger.
- Plastic body, chemical-resistant.



CPX Series

BRANSON

CPX Series (Digital timer)

Ordering Part No.	Voltage	Model 1800	Model 2800	Model 3800	Model 5800	Model 8800
	120 V	CPX1800	CPX2800	CPX3800	CPX5800	CPX8800
Part No.		CPX-952-119R	CPX-952-219R	CPX-952-319R	CPX-952-519R	CPX-952-819R
	230/240 V	СРХ1800-Е	СРХ2800-Е	СРХ3800-Е	СРХ5800-Е	СРХ8800-Е
Part No.		CPX-952-139R	CPX-952-239R	CPX-952-339R	CPX-952-539R	CPX-952-839R

Specifications

	Model 1800	Model 2800	Model 3800	Model 5800	Model 8800
Tank Capacity					
Liters/Gallons	1.9/0.5	2.8/0.75	5.7/1.5	9.5/2.5	20.8/5.5
Tank Size (L/W/D)					
Inches	6 x 5.5 x 4	9.5 x 5.5 x 4	11.5 x 6 x 6	11.5 x 9.5 x 6	19.5 x 11.5 x 6
mm	150 x 140 x 100	230 x 140 x 100	290 x 150 x 150	290 x 240 x 150	495 x 290 x 150
Overall Size (L/W/D)					
Inches	9.9 x 12 x 11.9	13.3 x 12 x 11.9	15.6 x 12.5 x 14.8	15.6 x 15.8 x 14.9	23.5 x 18.3 x 15.4
mm	251 x 304 x 302	337 x 304 x 302	397 x 317 x 377	397 x 401 x 378	596 x 466 x 391
Weight					
Pounds/Kilograms	7/3.2	9/4.1	12/5.4	14/6.4	26/11.8
Frequency	40 kHz	40 kHz	40 kHz	40 kHz	40 kHz
Drain	No	No	Yes	Yes	Yes

NOTE: Tank cover included. For optimum cleaning results, Branson offers a line of accessories including perforated trays, solid trays, beaker covers and support racks for your application needs.

Americas

Branson Ultrasonics Corp. 41 Eagle Road Danbury, CT 06810, USA T: 203-796-0400 F: 203-796-2250 Toll Free: 800-732-9262 www.bransonultrasonics.com

Standard-two year warranty.

All specifications subject to change without notice. All dimensions are nominal. All ultrasonic baths meet FCC, CSA, CE & UL rules and regulations.

Europe and Africa

Branson Ultrasonic SA Ch. du Faubourg-de-Cruseilles 9 1227 Carouge Switzerland T: +41(0)22 3048358 F: +41(0)22 3048359 www.branson.ch

Asia

Branson Ultrasonics (Shanghai) Co., Ltd. 758 Rong Le Dong Road Song Jiang, Shanghai, PRC, 201613 T: 86-21-3781-0588 F: 86-21-5774-5100 www.branson.com.cn





Printed in the U.S.A. BCL-0002-12