

Model BF 260 | Standard-Incubators with forced convection

The BINDER incubator of the BF Avantgarde. Line series with forced convection is suitable for all gentle incubation applications, particularly under a full load and large batch throughputs. This incubator is extremely homogeneous and has quick recovery times.

BENEFITS

- Excellent temporal and spatial temperature accuracy
- · High process reliability
- 100°C disinfection routine



Model 260



Model 260

IMPORTANT FEATURES

- Temperature range: +7°C above ambient temperature to +100°C
- High temperature accuracy thanks to APT.line™ technology
- Forced convection
- Controller with LCD display
- Electromechanical control of the exhaust air flap
- Inner door made of tempered safety glass

- 2 chrome-plated racks
- Class 3.1 integrated independent temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- USB port for recording data

ORDERING INFORMATION

Interior volume [L]	Power supply - unit fuse	Plug*	Version	Model version	ArtNo.
Model BF 260					
	120 V 1~ 60 Hz -12,5 A	NEMA 5-15	Standard	BF260UL-120V	9010-0320
257	230 V 1~ 50/60 Hz -8,0 A	CEE 7/7	Standard	BF260-230V	9010-0319



TECHNICAL DATA


TECHNICAL DATA				
Data				
Designation	BF260-230V	BF260UL-120V		
Article Number	9010-0319	9010-0320		
Option model	Standard	Standard		
Performance Data Temperature				
Temperature range	+7 °C above ambient temperature to 100 °C	+7 °C above ambient temperature to 100 °C		
Temperature uniformity at 37°C	0.2 ± K	0.2 ± K		
Temperature uniformity at 100°C	1.2 ± K	1.2 ± K		
Temperature fluctuation at 37°C	0.1 ± K	0.1 ± K		
Temperature fluctuation at 100°C	0.3 ± K	0.3 ± K		
Heating up time to 100°C	30 min	30 min		
Heating up time to 37°C	7 min	7 min		
Recovery time after door was opened for 30 s at 37°C	3 min	3 min		
Electrical data				
Rated Voltage	230 V	120 V		
Power frequency	50/60 Hz	60 Hz		
Nominal power	0,9 kW	1 kW		
Unit fuse	8,o A	12,5 A		
Phase (Nominal voltage)	1~	1~		
Dimensions and weights				
Interior volume	257 L	257 L		
Net weight of the unit (empty)	85 kg	85 kg		
Load per rack	40 kg	40 kg		
Permitted load	270 kg	270 kg		
Wall clearance back	160 mm	160 mm		
Wall clearance sidewise	100 mm	100 mm		
Housing dimensions not incl. fittings and connections				
Width net	810 mm	810 mm		
Height net	845 mm	845 mm		



Depth net	760 mm	760 mm
Internal Dimensions		
Interior width	650 mm	650 mm
Interior height	780 mm	780 mm
Interior depth	510 mm	510 mm
Inner doors	1	1
Unit doors	1	1
Environment-specific data		
Sound-pressure level	43 dB(A)	43 dB(A)
Energy consumption at 100°C	275 Wh/h	275 Wh/h
Energy consumption at 37°C	65 Wh/h	65 Wh/h
Fixtures		
Number of shelves (std./max.)	2/8	2/8

All technical data is specified for unloaded units with standard equipment at an ambient temperature of ± 22 °C ± 3 °C and a power supply voltage fluctuation of ± 10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS Incl. fittings and connections [mm]



OPTIONS

Designation	Description	BF 260	*	ArtNo.
Access port with silicone plug	left			
	10 mm	•	01	8012-1274
	30 mm	•	01	8012-1156
	50 mm	•	01	8012-1164
	right			
	10 mm	•	01	8012-1267
	30 mm	•	01	8012-1153



Designation	Description	BF 260	*	ArtNo.
	50 mm	•	01	8012-1162
	top			
	10 mm	•	01	8012-1261
	30 mm	•	01	8012-1150
	50 mm	•	01	8012-1159
	100 mm	•	01	8012-1166
Alarm function for overheating	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device	•	-	8012-1634
Analog output 4-20 mA	for temperature values (output not adjustable)	•	02	8012-1622
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	•	-	8012-1111
Calibration certificate, temperature	for temperature, measurement in center of chamber at specified temperature	•	-	8012-1130
	temperature measurement incl. certificate, 9 measuring points at specified temperature	•	-	8012-1548
	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	•	-	8012-1569
	temperature measurement incl. certificate and 27 measuring points at specified temperature	•	-	8012-1590
Clock	battery-backed	•	-	8012-1639
Door lock	lockable door handle	•	-	8012-1663
Ethernet interface	for Multi Management Software APT-COM™	•	-	8012-0990
Gas-tight option model	Incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	•	-	8012-1046
Inert gas connection	With gas inlet and outlet, \emptyset 10 mm, incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	•	-	8012-1049
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	•	-	8012-1618

ACCESSORIES

Designation	Description	BF 260	*	ArtNo.
APT-COM™ 4 BASIC-Edition	for simple logging and documentation requirements with up to 5 networked units.			
	version 4, BASIC edition	•	-	9053-0039
APT-COM™ 4 GLP-Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper- proof way in line with the requirements of FDA Regulation 21 CFR 11.			
	version 4, GLP edition	•	-	9053-0042



Description	BF 260	*	ArtNo.
convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.			
version 4, PROFESSIONAL edition	•	-	9053-0040
concentrated, for gentle remove of residual contaminants; 1 kg		-	8012-2250
IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit			
Digital in PDF format	•	-	7057-0005
Hard copy inside folder	•	-	7007-0005
IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit			
Digital in PDF format	•	-	7057-0001
Hard copy inside folder	•	-	7007-0001
max. load per rack 40 kg			
chrome plated	•	-	8012-2042
stainless steel	•	-	8012-2169
max. load per rack 70 kg			
Stainless steel	•	-	8012-2184
Rubber pads set anti-slip feet		-	8012-2030
max. load per rack 40 kg			
Stainless steel	•	-	8012-2177
stable cart, casters with locking brakes, dimensions: W 1,300 x D 800 x H 780 mm	•	-	9051-0019
	to 100 units. version 4, PROFESSIONAL edition concentrated, for gentle remove of residual contaminants; 1 kg IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO ₂ , O ₂ – or pressure, depending on unit Digital in PDF format Hard copy inside folder IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit Digital in PDF format Hard copy inside folder max. load per rack 40 kg chrome plated stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel	to 100 units. version 4, PROFESSIONAL edition concentrated, for gentle remove of residual contaminants; 1 kg · IQ/QQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/QQ; parameters: temperature, CO ₂ , O ₂ – or pressure, depending on unit Digital in PDF format Hard copy inside folder IQ/QQ documents – supporting documents for validation performed by customers, consisting of: IQ/QQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit Digital in PDF format Hard copy inside folder max. load per rack 40 kg chrome plated stainless steel max. load per rack 70 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg	to 100 units. version 4, PROFESSIONAL edition concentrated, for gentle remove of residual contaminants; 1 kg . IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO ₂ , O ₃ – or pressure, depending on unit Digital in PDF format Hard copy inside folder IQ/OQ documents – supporting documents for validation performed by customers, consisting of IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₃ , pressure, depending on unit Digital in PDF format Hard copy inside folder max. load per rack 40 kg chrome plated stainless steel max. load per rack 70 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg Stainless steel set anti-slip feet max. load per rack 40 kg

SERVICES

Designation	Description	*	ArtNo.
Calibration services			
C. Uhartina artificata Assaulata	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	05	DL30-0120
Calibration certificate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	05	DL30-0102
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	05	DL30-0109
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	05	DL30-0118



Designation	Description	*	ArtNo.
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	05	DL30-0127
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance contracts			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0720
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0910
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0810
Maintenance services			
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-0602
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	05	DL40-0100
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
Warranty service			
1-year warranty extension	The warranty is extended by 1 year from the delivery date, wear parts are excluded	05	DL50-0010



NOTES

- O1 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 info@binder-world.com www.binder-world.com BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us BINDER Environmental Testing Equipment (Shanghai) Co., Ltd.

Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com