

Model ED 400 | Drying and heating chambers with natural convection

The strengths of a BINDER ED series drying chamber include routine drying and sterilization tasks up to +300 °C. Thanks to the natural convection, all thermal processes which use this drying chamber are highly efficient. The ED series ensures fast, uniform drying.

BENEFITS

- Uniform drying conditions thanks to APT.line™ technology
- Identical test conditions throughout the chamber interior independent of sample size and quantity
- · Outstanding thermal insulation saves operation costs



Model 400

IMPORTANT FEATURES

- Temperature range: +5°C above ambient temperature to +300 °C
- APT.line™ preheating chamber technology
- Natural convection
- Adjustable exhaust air flap

- Controller with timer functions
- 2 chrome-plated racks
- Class 2 independent adjustable temperature safety device (DIN 12880) with visual alarm

ORDERING INFORMATION

Interior volume [L]	Power supply - unit fuse	Plug*	Version	Model version	ArtNo.
Model ED 400					
	208 V 3~ 60 Hz -16,0 A	NEMA L21-20	with RS 422	ED400UL-208V-I	9010-0168
400	400 V 3~/N/PE 50/60 Hz -16,0 A	CEE 16 / 6 H plug 5- pin	with RS 422	ED400-400V-I	9010-0075



TECHNICAL DATA


TECHNICAL DATA		
Data		
Designation	ED400-400V-I	ED400UL-208V-I
Article Number	9010-0075	9010-0168
Option model	with RS 422	with RS 422
Performance Data Temperature		
Temperature range	+5 °C above ambient temperature to 300 °C	+5 °C above ambient temperature to 300 °C
Temperature uniformity at 150°C	3.0 ± K	3.0 ± K
Temperature fluctuation at 150°C	0.5 ± K	0.5 ± K
Heating up time to 150°C	71 min	71 min
Recovery time after door was opened for 30 s at 150°C	31 min	31 min
Air change data		
Air change rate at 150°C	10 X/h	10 x/h
Electrical data		
Rated Voltage	400 V	208 V
Power frequency	50/60 Hz	60 Hz
Nominal power	3,4 kW	3.4 kW
Unit fuse	16,0 A	16,0 A
Phase (Nominal voltage)	3~/N/PE	3~
Dimensions and weights		
Interior volume	400 L	400 L
Net weight of the unit (empty)	125 kg	125 kg
Load per rack	35 kg	35 kg
Permitted load	90 kg	90 kg
Wall clearance back	160 mm	160 mm
Wall clearance sidewise	100 mm	100 mm
Housing dimensions not incl. fittings and connections		
Width net	1,235 mm	1,235 mm
Height net	1,025 mm	1,025 mm
Depth net	765 mm	765 mm
Internal Dimensions		



Interior width	1,000 mm	1,000 mm
Interior height	800 mm	800 mm
Interior depth	520 mm	520 mm
Unit doors	2	2
Environment-specific data		
Energy consumption at 150°C	672 Wh/h	672 Wh/h
Fixtures		
Number of shelves (std./max.)	2/10	2/10

All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10%. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS Incl. fittings and connections [mm]



OPTIONS

Designation	Description	ED 400	*	ArtNo.
	back			
	10 mm	•	01	8012-1282
	30 mm	•	01	8012-0540
	50 mm	•	01	8012-0546
Access port with silicone plug	left			
	10 mm	•	01	8012-1275
	30 mm	•	01	8012-0537
	50 mm	•	01	8012-0542
	100 mm	•	01	8012-0722
	right			
	10 mm	•	01	8012-1268
	30 mm	•	01	8012-0536
	50 mm	•	01	8012-0541



Designation	Description	ED 400	*	ArtNo.
	100 mm	•	01	8012-0721
	top			
	10 mm	•	01	8012-1262
	30 mm	•	01	8012-0539
	50 mm	•	01	8012-0545
	100 mm	•	01	8012-0547
	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device			
Name function for available	120/208 V option model	•	-	8012-1303
Alarm function for overheating	switchable acoustic alarm, with adjustable limit value on the independent temperature safety device. Not in combination with the following option: Door with window			
	230/400 V option model	•	-	8012-1299
Analog output 4-20 mA	for temperature values (output not adjustable)	•	-	8012-0430
Calibration certificate,	for temperature; for extending the measurement in center of chamber to include another test temperature	•	-	8012-1115
	for temperature, measurement in center of chamber at specified temperature	•	-	8012-1134
Calibration certificate,	temperature measurement incl. certificate, 9 measuring points at specified temperature	•	-	8012-1551
emperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	•	-	8012-1572
	temperature measurement incl. certificate and 27 measuring points at specified temperature	•	-	8012-1593
Class 3.1 independent emperature safety device	with visual alarm (DIN 12880)	•	-	8012-0032
Door gasket	made of FKM, silicone-free	•	-	8012-0497
Door lock	lockable door handle	•	-	8012-1253
nner chamber, reinforced	including 2 reinforced racks	•	-	8012-1730
Measurement of air exchange ate	in accordance with ASTM D5374, definition and protocol according to ambient temperature	•	-	8012-0195
Pt 100 temperature sensor	additional flexible Pt 100, interior, with external connection incl. LEMO connector (3-pin)	•	-	8012-1173
/iewing window and interior	Viewing window 290 x 470 mm in every door and interior lighting 30 W. Not in combination with the following option: Alarm function for overheating			
ghting	400 V option model	•	-	8012-0269



ACCESSORIES

Designation	Description	ED 400	*	ArtNo.
	for simple logging and documentation requirements with up to 5 networked units.			
APT-COM™ 4 BASIC-Edition	version 4, BASIC edition	•	-	9053-0039
APT-COM™ 4 GLP-Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper- proof way in line with the requirements of FDA Regulation 21 CFR 11.			
	version 4, GLP edition	•	-	9053-0042
APT-COM™ 4 PROFESSIONAL-	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.			
Edition	version 4, PROFESSIONAL edition	•	-	9053-0040
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	•	-	8012-2250
Qualification documents	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit			
	Digital in PDF format	•	-	7057-0005
	Hard copy inside folder	•	-	7007-0005
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, $\mathrm{CO_2}$, $\mathrm{O_2}$, pressure, depending on unit			
	Digital in PDF format	•	-	7057-0001
	Hard copy inside folder	•	-	7007-0001
0.1	chrome plated	•	-	8012-2036
Rack	stainless steel	•	-	8012-2159
Shelf, perforated	Stainless steel	•	-	8012-2162
Table on castors	stable cart, casters with locking brakes, dimensions: W 1,300 x D 800 x H 780 mm	•	-	9051-0019

SERVICES

Designation Description		*	ArtNo.
Calibration services			
Calibration certificate, temperature	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	05	DL30-0110
	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	05	DL30-0102
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	05	DL33-0000
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	05	DL30-0109



Designation	Description	*	ArtNo.
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	05	DL30-0118
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	05	DL30-0127
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance contracts			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0720
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0915
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0815
Maintenance services			
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-0601
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	05	DL40-0100
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
Warranty service			
1-year warranty extension	The warranty is extended by 1 year from the delivery date, wear parts are excluded	05	DL50-0010



NOTES

- O1 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 info@binder-world.com www.binder-world.com BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us BINDER Environmental Testing Equipment (Shanghai) Co., Ltd.

Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com