Model FD 115 | Drying and heating chambers with forced convection

A BINDER FD series Avantgarde.Line heating oven is always used when fast drying and sterilization is required. Thanks to its fully homogeneous temperature distribution, quick dynamics and powerful fan, this heating oven saves valuable time.

BENEFITS

- Best energy efficiency on the market
- Excellent temporal and spatial temperature accuracy
- USB connection for recording data
- Temperature range up to +300 °C



Model 115

IMPORTANT FEATURES

- Temperature range: +10°C above ambient temperature to +300 °C
- Up to 30% lower energy consumption compared to conventional units on the stackable
 Stackable
 Class 2 int
- High temperature accuracy thanks to APT.line™ technology
- Forced convection
- Controller with LCD display
- Electromechanical control of the exhaust air flap

- 2 chrome-plated racks
- Stackable
- Class 2 integrated independent adjustable temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- USB port for recording data

ORDERING INFORMATION

Interior volume [L]	Power supply - unit fuse	Plug*	Version	Model version	ArtNo.
Model FD 115					
,	120 V 1~ 60 Hz -12,5 A	NEMA 5-15	Standard	FD115UL-120V	9010-0306
116	230 V 1~ 50/60 Hz -6,3 A	CEE 7/7	Standard	FD115-230V	9010-0305

BINDER Best conditions for your success

TECHNICAL DATA

Data


Data		
Designation	FD115-230V	FD115UL-120V
Article Number	9010-0305	9010-0306
Option model	Standard	Standard
Performance Data Temperature		
Temperature range	+10 °C above ambient temperature to 300 °C	+10 °C above ambient temperature to 300 °C
Temperature uniformity at 150°C	1.7 ± K	1.7 ± K
Temperature fluctuation at 150°C	0.3 ± K	0.3 ± K
Heating up time to 150°C	18 min	18 min
Recovery time after door was opened for 30 s at 150°C	4 min	4 min
Air change data		
Air change rate at 100°C	32 x/h	32 x/h
Electrical data		
Rated Voltage	230 V	120 V
Power frequency	50/60 Hz	60 Hz
Nominal power	1,3 kW	1,4 kW
Unit fuse	6,3 A	12,5 A
Phase (Nominal voltage)	1~	1~
Dimensions and weights		
Interior volume	116 L	116 L
Net weight of the unit (empty)	54 kg	54 kg
Load per rack	30 kg	30 kg
Permitted load	150 kg	150 kg
Wall clearance back	160 mm	160 mm
Wall clearance sidewise	100 mm	100 mm
Housing dimensions not incl. fittings and connections		
Width net	710 mm	710 mm
Height net	735 mm	735 mm
Depth net	605 mm	605 mm
Internal Dimensions		



Interior width	550 mm	550 mm
Interior height	550 mm	550 mm
Interior depth	385 mm	385 mm
Unit doors	1	1
Environment-specific data		
Sound-pressure level	43 dB(A)	43 dB(A)
Energy consumption at 100°C	215 Wh/h	215 Wh/h
Energy consumption at 150°C	340 Wh/h	340 Wh/h
Fixtures		
Number of shelves (std./max.)	2/5	2/5

All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS Incl. fittings and connections [mm]



OPTIONS

Designation	Description	FD 115	*	ArtNo.
	left			
	10 mm	•	01	8012-1276
	30 mm	•	01	8012-1016
		•	01	8012-1020
	100 mm	•	01	8012-1027
Access port with silicone plug	right			
	10 mm	•	01	8012-1269
	30 mm	•	01	8012-1015
		•	01	8012-1019
	100 mm	•	01	8012-1028

BINDER Best conditions for your success

Designation	Description	FD 115	*	ArtNo.
	top			
	10 mm	•	01	8012-1263
	30 mm	•	01	8012-1364
	50 mm	•	01	8012-1380
	100 mm	•	01	8012-1671
Alarm function for overheating	switchable acoustic alarm, with adjustable limit value on the independent temperature safety device. Not in combination with the following option: Door with window	•	-	8012-1636
Analog output 4-20 mA	for temperature values (output not adjustable)	•	02	8012-1624
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	•	-	8012-1116
	for temperature, measurement in center of chamber at specified temperature	•	-	8012-1135
Calibration certificate,	temperature measurement incl. certificate, 9 measuring points at specified temperature	•	-	8012-1552
emperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	•	-	8012-1573
	temperature measurement incl. certificate and 27 measuring points at specified temperature	•	-	8012-1594
Class 3.1 independent emperature safety device	with visual alarm (DIN 12880)	•	-	8012-1643
Clock	battery-backed	•	-	8012-1641
Door gasket	made of FKM, silicone-free	•	-	8012-1650
Door lock	lockable door handle	•	-	8012-1665
Ethernet interface	for Multi Management Software APT-COM™	•	-	8012-0988
Gas-tight option model	Incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	•	-	8012-1685
Heating output, reinforced	for faster heating up time and improved recovery time; max. 300°C			
leating output, reinforced	120/230 V option model	•	-	8012-1057
HEPA air filter	On fresh air supply for unit; filter classification H14 (acc. to. EN 1822-1:2009, > 99.995% at 0.3 μm); not in conjunction with reinforced heating output, reinforced fan	•	-	8012-1051
nert gas connection	With gas inlet and outlet, Ø 10 mm, incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	•	-	8012-1691
nner chamber, reinforced	max. total load 170 kg	•	-	8012-1054
	with 25 W light bulb			
nterior lighting	120 V option model	•	-	8012-1632
	with 27 W light bulb			

BINDER Best conditions for your success

Designation	ation Description		*	ArtNo.
	230/240 V option model	•	-	8012-1628
Measurement of air exchange rate	in accordance with ASTM D5374, definition and protocol according to ambient temperature	•	-	8012-1195
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	•	-	8012-1620
	Viewing window (triple-glazed insulating glass) 370 x 370 mm in the door and interior lighting 15 W. Not in combination with the following option: Alarm function for overheating			
Viewing window and interior lighting	120 V option model	•	-	8012-1706
	230 V option model	•	-	8012-1704

ACCESSORIES

Designation	Description	FD 115	*	ArtNo.
	for simple logging and documentation requirements with up to 5 networked units.			
APT-COM™ 4 BASIC-Edition	version 4, BASIC edition	•	-	9053-0039
APT-COM™ 4 GLP-Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper- proof way in line with the requirements of FDA Regulation 21 CFR 11.			
	version 4, GLP edition	•	-	9053-0042
APT-COM™ 4 PROFESSIONAL-	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.			
Edition	version 4, PROFESSIONAL edition	•	-	9053-0040
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	•	-	8012-2250
	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit			
	- Digital in PDF format	•	-	7057-0005
	- Hard copy inside folder	•	-	7007-0005
Qualification documents	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO_2 , O_2 , pressure, depending on unit			
	- Digital in PDF format	•	-	7057-0001
	- Hard copy inside folder	•	-	7007-0001
	max. load per rack 30 kg			
Rack	- chrome plated	•	-	8012-2040
	- stainless steel	•	-	8012-2168

BINDER Best conditions for your success

Designation	Description	FD 115	*	ArtNo.
Rubber pads	set anti-slip feet	•	-	8012-2030
	max. load per rack 30 kg			
Shelf, perforated	Stainless steel	•	-	8012-2176
Table on castors	stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm	•	-	9051-0018

SERVICES

Designation	Description	*	ArtNo.
Calibration services			
Calibration certificate, temperature	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	05	DL30-0120
campitation certaincate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	05	DL30-0102
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	05	DL33-0000
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	05	DL30-0109
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	05	DL30-0118
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	05	DL30-0127
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance contracts			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0720
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0910
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0810
Maintenance services			
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-0602

BINDER Best conditions for your success

Designation	Description	*	ArtNo.
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	05	DL40-0100
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
Warranty service			
1-year warranty extension	The warranty is extended by 1 year from the delivery date, wear parts are excluded	05	DL50-0010



NOTES

- 01 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- O5 Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com

BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us

BINDER Environmental Testing

Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com