

Model KB 260 | Cooling incubators with a large temperature range

The powerful virtuoso in cooling incubators for microorganisms: KB units are able to incubate with exceptional precision even when fully loaded, feature a hot-air disinfection routine, and can be programmed for weekend operation with ease. The new KB unit consumes as much as 40% less energy than the previous model.

BENEFITS

- Assured: highly precise incubation conditions thanks to power reserves
- · Reliable: failsafe operation over the long term thanks to proven compressor technology and interior made of stainless steel
- Smart: hot-air disinfection and easy programming of a second set temperature
- Economical: up to 40% lower energy consumption than the previous model thanks to modern inverter cooling technology







Model 260

IMPORTANT FEATURES

- Temperature range: o °C to +70 °C
- Proven APT.line™ preheating chamber technology
- Up to 40% lower energy consumption compared to the previous model
- Energy-efficient cooling with modern inverter cooling unit
- Cooling with climate-neutral R-600a refrigerant
- · Door heating to prevent condensation
- Sturdy housing design with HIT sandwich technology
- Interior made completely of stainless steel
- · Inner doors made of metal oxide-coated safety glass

- Two racks made of stainless steel
- 80 mm x 45 mm access port with silicone plug
- · Floor-standing units featuring sturdy twin casters with brakes at the front
- Simple programming of a second set temperature value
- Internal data logger, measured values can be read out in open format via USB
- Class 3.3 independent temperature safety device (DIN 1288o) with visual and acoustic alarms
- Unit self-test for comprehensive status analysis
- · Data interfaces: Ethernet, USB

ORDERING INFORMATION

Interior volume [L]	Power supply - unit fuse	Plug*	Version	Model version	ArtNo.
Model KB 260					
	120 V 1~ 50/60 Hz -16,0 A	NEMA 5-20	Standard	KB260UL-120V	9020-0501
262	220240 V 1~ 50/60 Hz -16,0 A	CEE 7/7	Standard	KB260-230V	9020-0473



TECHNICAL DATA


TECHNICAL DATA					
Data					
Designation	KB260-230V	KB260UL-120V			
Article Number	9020-0473	9020-0501			
Option model	Standard	Standard			
Performance Data Temperature					
Temperature range	o70 °C	o70 °C			
Temperature uniformity at 37°C	0.2 ± K	0.2 ± K			
Temperature fluctuation at 37°C	0.1 ± K	0.1 ± K			
Max. heat compensation at 37°C	410 W	410 W			
Recovery time after door was opened for 30 s at 37°C	3 min	3 min			
Electrical data					
Rated Voltage	220240 V	120 V			
Power frequency	50/60 Hz	50/60 Hz			
Nominal power	1,3 kW	1,3 kW			
Unit fuse	16,0 A	16,0 A			
Phase (Nominal voltage)	1~	1~			
Dimensions and weights	Dimensions and weights				
Interior volume	262 L	262 L			
Net weight of the unit (empty)	174 kg	174 kg			
Load per rack	30 kg	30 kg			
Permitted load	90 kg	90 kg			
Wall clearance back	100 mm	100 mm			
Wall clearance sidewise	180 mm	180 mm			
Housing dimensions not incl. fittings and connections					
Width net	930 mm	930 mm			
Height net	1,396 mm	1,396 mm			
Depth net	900 mm	900 mm			
Internal Dimensions					
Interior width	656 mm	656 mm			
Interior height	695 mm	695 mm			



Interior depth	575 mm	575 mm
Inner doors	1	1
Unit doors	1	1
Environment-specific data		
Sound-pressure level at 25°C	50 dB(A)	50 dB(A)
Energy consumption at 37°C	140 Wh/h	165 Wh/h
Fixtures		
Number of shelves (std./max.)	2/9	2/9

All technical data is specified for unloaded units with standard equipment at an ambient temperature of $\pm 2^{\circ}$ C $\pm 3^{\circ}$ C and a power supply voltage fluctuation of $\pm 10^{\circ}$ M. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS Incl. fittings and connections [mm]



OPTIONS

Designation	Description	KB 260	*	ArtNo.
	left			
	30 mm	•	01	8012-2465
	50 mm	•	01	8012-2466
	100 mm	•	01	8012-2467
Access port with silicone plug	right			
	30 mm	•	01	8012-2468
	50 mm	•	01	8012-2469
	100 mm	•	01	8012-2470
	top			
	30 mm	•	01	8012-2497
	50 mm	•	01	8012-2471



Designation	Description	KB 260	*	ArtNo.
	100 mm	•	01	8012-2472
Alarm output, zero-voltage	Accessible via 3-pin clamping sleeve (max. 24 V - 2.5 A), with acoustic signal that can be switched off	•	-	8012-2370
Analog output 4-20 mA	for temperature values (output not adjustable)	•	-	8012-2371
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	•	-	8012-2372
Calibration certificate, temperature	for temperature, measurement in center of chamber at specified temperature	•	-	8012-2571
	temperature measurement incl. certificate, 9 measuring points at specified temperature	•	-	8012-2376
	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	•	-	8012-2380
	temperature measurement incl. certificate and 27 measuring points at specified temperature	•	-	8012-2424
Door lock	lockable door handle	•	-	8012-2529
Door lock, electromechanical	can be opened with PIN code via controller	•	-	8012-2531
Inner chamber, reinforced	max. total load 180 kg	•	-	8012-2507
nterior lighting	With climate-resistant LEDs, switches when the unit door is opened	•	-	8012-2559
Shipping pallet	with unloading ramp for installing unit without forklift	•	-	8012-2545
Specimen temperature display	Flexible Pt 100 indoor temperature sensor, for object temperature display or control	•	-	8012-2549
Swivel casters, height- idjustable	For horizontal alignment of the unit on uneven floors	•		8012-2541

ACCESSORIES

Designation	Description		*	ArtNo.
	for simple logging and documentation requirements with up to 5 networked units.			
APT-COM™ 4 BASIC-Edition	version 4, BASIC edition	•	-	9053-0039
APT-COM™ 4 GLP-Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper- proof way in line with the requirements of FDA Regulation 21 CFR 11.			
	version 4, GLP edition	•	-	9053-0042
APT-COM™ 4 PROFESSIONAL- Edition	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.			
	version 4, PROFESSIONAL edition	•	-	9053-0040
LED light bars	Basic set consisting of 2 pieces, attachment material, control unit for max. 4 light strips, 100-240 V, 50/60 Hz			
	Basic set 300, length 30 cm	•	-	8012-1107



Designation	Description	KB 260	*	ArtNo.
	Basic set 500, length 50 cm	•	-	8012-1108
	Expansion set consisting of 2 pieces, attachment material: clips. For expanding the basic set of light bars			
	Expansion set 300, length 30 cm	•	-	8012-1716
	Expansion set 500, length 50 cm	•	-	8012-1717
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	•	-	8012-2250
	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit			
	Digital in PDF format	•	-	7057-0005
Qualification documents	Hard copy inside folder	•	-	7007-0005
Qualification documents	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO_2 , O_2 , pressure, depending on unit			
	Digital in PDF format	•	-	7057-0001
	Hard copy inside folder	•	-	7007-0001
Reinforced rack	Shelf rack in set with pair of retaining rails (U rails), made entirely of stainless steel			
Remoted fack	Load-bearing capacity 80 kg	•	-	8012-2413
Shelf rack, perforated	Shelf rack in set with pair of retaining rails (U rails), made entirely of stainless steel			
	Load-bearing capacity 40 kg	•	-	8012-2407
Standard rack	Shelf rack in set with pair of retaining rails (ball bearing mounted telescopic rails), made entirely of stainless steel			
	Load-bearing capacity 40 kg	•	-	8012-2384
	Shelf rack in set with pair of retaining rails (U rails), made entirely of stainless steel			
	Load-bearing capacity 40 kg	•	-	8012-2390

SERVICES

Designation	Description	*	ArtNo.
Calibration services			
	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	05	DL30-0135
Calibration certificate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	05	DL30-0102
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	05	DL30-0109



Description	*	ArtNo.
Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	05	DL30-0118
Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	05	DL30-0127
Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0720
Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0945
Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0845
One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-0604
Execution of IQ/OQ in accordance with qualification folder	05	DL41-0200
Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
The warranty is extended by 1 year from the delivery date, wear parts are excluded	05	DL50-0010
	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate Temperature measurement with 27 measuring points with a set value specified by the user, including certificate Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work) Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate Execution of IQ/OQ/PQ in accordance with qualification folder Execution of IQ/OQ/PQ in accordance with qualification folder	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate Temperature measurement with 27 measuring points with a set value specified by the user, including certificate Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions, (excl.: unpacking, setup, controller instructions, programming, installation work) Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate Description of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate



NOTES

- O1 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 info@binder-world.com www.binder-world.com BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us BINDER Environmental Testing Equipment (Shanghai) Co., Ltd.

Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com